

MLCC Case-V-Cap	MLCC Case	MLCC V	MLCC Cap uF	MnO2	MnO2	MnO2	Polymer	OxiCap
1210 6 476	1210	6	47	TAJB476M006RNJ	TAJB476M010RNJ	F930J476MBA	TCJB476M006R0070	NOJB476M006R
1210 6 475	1210	6	4.7		TAJB475M016RNJ	F931D475MBA		
1210 6 226	1210	6	22		TAJB226M010RNJ	F931A226MBA	TCJB226M010R0300	NOJB226M006R
1210 6 107	1210	6	100	TAJB107M006RNJ	TAJB107M010RNJ	F930J107MBA	TCJB107M006R0070	NOJB107M006R
1210 6 106	1210	6	10		TAJB106M016RNJ	F931C106MBA		NOJB106M010R
1210 6 105	1210	6	1		TAJB105M035RNJ			
1210 4 476	1210	4	47		TAJB476M010RNJ	F920G476MBA	TCJB476M006R0070	NOJB476M004R
1210 4 475	1210	4	4.7		TAJB475M016RNJ	F931D475MBA		
1210 4 226	1210	4	22		TAJB226M010RNJ	F931A226MBA	TCJB226M010R0300	NOJB226M004R
1210 4 107	1210	4	100	TAJB107M004RNJ	TAJB107M010RNJ	F930G107MBA	TCJB107M004R0070	NOJB107M004R
1206 6 476	1206	6	47	TAJA476M006RNJ		F930J476MAA	TCJA476M006R0100	
1206 6 475	1206	6	4.7		TAJR475M010RNJ	F931A475MAA		NOJA475M006R
1206 6 226	1206	6	22	TAJA226M006RNJ	TAJA226M010RNJ	F930J226MAA	TCJA226M006R0300	NOJA226M006R
1206 6 225	1206	6	2.2		TAJA225M016RNJ	F931C225MAA		
1206 6 107	1206	6	100			F930J107MAA	TCJA107M006R0100	
1206 6 106	1206	6	10	TAJA106M006RNJ		F930J106MAA	TCJA106M006R0300	NOJA106M006R
1206 4 476	1206	4	47	TAJA476M004RNJ	TAJA476M006RNJ	F930G476MAA	TCJA476M004R0200	NOJA476M006R
1206 4 226	1206	4	22	TAJA226M004RNJ	TAJA226M006RNJ	F930G226MAA	TCJ226M004R0300	NOJA226M004R
1206 4 107	1206	4	100	TAJA107M004RNJ	TAJA107M006RNJ	F930G107MAA	TCJA106M004R0200	
1206 4 106	1206	4	10		TAJA106M006RNJ	F930J106MAA	TCJA106M006R0300	NOJA106M006R
0805 6 475	0805	6	4.7	TAJR475M006RNJ	TAJR475M010RNJ	F920J475MPA		NOJP475M006R
0805 6 226	0805	6	22	TAJP226M006RNJ		F981A226MSA	F380J226MSA	
0805 6 225	0805	6	2.2	TAJR225M006RNJ	TAJR225M010RNJ	F920J225MPA		
0805 6 106	0805	6	10	TAJR106M006RNJ	TAJR106M010RNJ	F920J106MPA		NOJP106R006R
0805 4 475	0805	4	4.7	TAJR475M004RNJ	TAJR475M006RNJ	F920G475MPA		NOJP475M006R
0805 4 226	0805	4	22	TAJR226M004RNJ	TAJR226M006RNJ	F920G226MPA	F380J226MSA	
0805 4 225	0805	4	2.2	TAJR225M004RNJ	TAJR225M006RNJ	F920J225MPA		NOJP225M010R
0805 4 106	0805	4	10	TAJR106M004RNJ	TAJR106M006RNJ	F920G106MPA		NOJP106M004R
0603 6 476	0603	6	47	TLCL476M006R		F980J476MMA	F380J476MMAAXE	
0603 6 475	0603	6	4.7	TLCL475M006R	TLCL475M010R	F980J475MMA	F381A475MMA	
0603 6 226	0603	6	22	TLCL226M006R		F980J226MMA	F380J226MMA	
0603 6 225	0603	6	2.2	TACL225M006R	TACL225M010R	F981A225MMA	F381A225MMA	
0603 6 106	0603	6	10	TACL106M006R	TACL106M010R	F980J106MMA	F380J106MMA	
0603 6 105	0603	6	1	TACL105M006R	TACL105M010R	F981C105MMA		
0603 4 476	0603	4	47	TLCL476M004R	TLCL476M006R	F980G476MMA	F380J476MMAAXE	
0603 4 475	0603	4	4.7	TACL475M004R	TACL475M006R	F980J475MMA	F381A475MMA	
0603 4 226	0603	4	22	TACL226M004R	TACL226M006R	F980G226MMA	F380J226MMA	
0603 4 225	0603	4	2.2	TACL225M004R	TACL225M006R	F981A225MMA	F381A225MMA	
0603 4 106	0603	4	10	TACJ106M004R	TLCL106M006R	F980J106MMA	F380J106MMA	
0402 6 475	0402	6	4.7	TLCK475M006R		F980J475MUA	F380J475MUA	
0402 6 474	0402	6	0.47	TACK474M010RTA		F981C474MUA		
0402 6 225	0402	6	2.2	TACK225M006RTA	TLCK225M010RTA	F981A225MUA		
0402 6 106	0402	6	10	TLCK106M006		F980J106MUALZT		
0402 6 105	0402	6	1	TACK105M006RTA			F380J105MUA	
0402 6 104	0402	6	0.1	TACK104M016RTA				
0402 4 475	0402	4	4.7	TLCK475M004RTA	TLCK475M006RTA	F980G475MUA	F380J475MUA	
0402 4 474	0402	4	0.47	TACK474M010RTA		F981C474MUA		
0402 4 225	0402	4	2.2	TACK225M006RTA		F981A225MUA		
0402 4 105	0402	4	1	TACK105M006RTA			F380J105MUA	