

Key Features

iServer Virtual Chart Recorders

iServer 1

iServer 2

- ✓ Built-in display: 16-character green LCD
- ✓ Built in web server
- ✓ Data storage: 2 GB (SD Card)
- ✓ Logging: 1 sample/sec (SD card models only)
- ✗ USB interface
- ✓ Up to 4 channels
- ✗ Measurement type: environmental, no added smart probes

- ✓ Built-in display: Large, easy-to-read full color LED
- ✓ Built in Web Server
- ✓ Data storage: 11 GB
- ✓ Logging: 1 sample/sec (all models)
- ✓ USB interface
- ✓ Up to 8 channels
- ✓ Measurement type: environmental and added smart probes

Relays and digital output are the same between models.

Replacement Products

SKU FAMILIES

[iTHX-W3 >](#)
[iBTX-W >](#)
[iBTHX-W >](#)
[iTHX-D3 >](#)
[iBTHX-D >](#)
[iBTX-D >](#)



**iS2
BASIC**
[iS2-THB-B >](#)

SKU FAMILIES

[iTHX-SD >](#)
[iBTX-SD >](#)



**iS2
STANDARD**
[iS2-THB-ST >](#)

SKU FAMILIES

[iSD-TH >](#)
[iSD-TC >](#)



**iS2
DELUXE**
[iS2-THB-DP >](#)
[iS2-THB-DTC >](#)